

Technical data sheet 520B

Specification Cantilever frame, mesh backrest

Dimensions in mm

	Seat:	H:	470
	odd.	W:	450
		D:	410
	Total:	H:	930
		W (no ArmR):	485
		D:	540
Packaging data	Weight:	kg	7,5
	Volume:	m³	0.4



Basic equipment		Benefit
Backrest	Meshback, black.	Colourfast and resistant to deep scratches and abrasions.
Upholstery	Seat upholstery: 55 mm foam.	Great seating comfort.
Frame	Tubular steel frame Ø 22 x 2,5 mm, powder coated as colour finish (plastic parts).	
Seat carrier.	Plastic.	
Stackability.	4 chairs.	Diverse use of space.
Plastic parts	Colour maintained throughout, black.	Colourfast and resistant to deep scratches and abrasions.
Materials	All materials are segregated and recyclable.	Environmentally friendly.
Standards	EN 16139 for visitor chairs. GS-Symbol for tested safety and tested for contaminants.	High-quality and great comfort.
Certification	Quality management system DIN EN ISO 9001:2008, VO (EG) No. 1221/2009 (EMAS), Environmental management system DIN EN ISO 14001:2009, OHSAS, EcoVadis gold, Commitment to sustainability. Blue Angel, Bifma e3 level Platin.	High-quality product.
Warranty and return	10 years warranty. Complete return and recycling guarantee.	Exchange of parts free of charge within the guaranteed periods.

Disassembly instructions are available upon request for any interstuhl product



Technical data sheet 520B

Specification Cantilever frame, mesh backrest

Dimensions in mm

470 Seat: H: W: 450 D: 410 Total: 930 H: W (no ArmR): 485 D: 540 Packaging data Weight: 7,5 kg Volume: т³ 0,4



	Benefit
Meshback, white, flame red, traffic orange, may green, beige grey, iron grey, cobalt blue, pastel blue.	
White.	Optical design.
Powder coated brilliant silver or chromed.	Optical design.
Felt glides for hard floors.	Ideal stability and protection of the floor.
Several fabric collections and leather in various	Individual design.
	green, beige grey, iron grey, cobalt blue, pastel blue. White. Powder coated brilliant silver or chromed. Felt glides for hard floors.

Disassembly instructions are available upon request for any interstuhl product