

Technical data sheet V101H

Specification Four legged with seat upholstered, wooden shell

Dimensions in mm	Backrest:	H:	420	
		Seat:	H: 450	
	Total:	W:	445	
		D:	415	
		H:	825	
		W (no ArmR):	510	
Packaging data	Weight:	kg	6,5	
		Volume:	m³	0,37



Basic equipment

Benefit

Seat and Backrest	Seat and backrest shell in ergonomically-formed wood, backrest height 380 mm.	
Upholstery	Seat upholstered.	Great seating comfort.
Frame	Chrome-plated frame with elliptically-shaped steel tube 30 x 15 x 2 mm. Technically patented.	Very high stability, longevity. High-quality look.
Stackability	Stacking height of the vertical stacking: 15 chairs.	Space-saving storage.
Wooden parts	Stained beech. 9-layer bonded plywood.	
Glides	Plastic glides for soft floors, black.	Optimum stability of the chair. Protection of the floor.
Materials	All materials are segregated and recyclable.	Environmentally friendly.
Materials	DIN EN 16139 four leg and cantilever. GS-symbol for tested safety, tested for contaminants.	High safety and comfort.
Certification	Quality management system DIN EN ISO 9001:2008, VO (EG) No. 1221/2009 (EMAS), Environmental management system DIN EN ISO 14001:2009, OHSAS, EcoVadis gold, Commitment to sustainability. Blue Angel.	High-quality product.
Warranty and return	10 years warranty. Complete return and recycling guarantee.	Exchange of parts, free of charge, within the guaranteed period.

Disassembly instructions are available upon request for any interstuhl product

Technical data sheet V101H

Specification Four legged with seat upholstered, wooden shell

Dimensions in mm	Backrest:	H:	420	
		Seat:	H:	450
			W:	445
			D:	415
	Total:	H:	825	
		W (no ArmR):	510	
D:		550		
Packaging data	Weight:	kg	6,5	
	Volume:	m³	0,37	



Options		Benefit
Wooden parts	Oak, American walnut.	Optical design.
Glides	Felt glides for hard floors, black.	Optimum stability of the chair. Protection of the floor.
Armrests/Accessories	Armrests with plastic pad, row connector, panic bolt.	Optimal function extension depending on individual usage.

Disassembly instructions are available upon request for any interstuhl product